

# MINI PAK'R™ Air Cushion Machine

Patents Pending

“SMART” MACHINE MAKES ALL TYPES  
OF AIR CUSHION PRODUCTS



Supplied By: **The Cary Company**

Ph: 630-629-6600

[www.thecarycompany.com](http://www.thecarycompany.com)

**CARY**

# MINI PAK'R™ Machine Can Produce Six Different Air Cushions



MINI PAK'R machine on optional Wall Mount.

The intelligently designed MINI PAK'R™ machine uses RFID technology to automatically select the right settings for the film you chose. Operation is simple: plug in the MINI PAK'R machine, load film and it's ready to go.



NOVUS Double Cushion® film for large void fill and to block and brace



NOVUS Quilt-Air® Large film for void fill and wrapping



NOVUS Quilt-Air® Small film for interleaving and wrapping



NOVUS Supertube® film for void fill and wrapping



CELL-O® EZ film (4" x 8" size) for small void fill



CELL-O® EZ film (8" x 8" size) for larger void fill and to block and brace

- **Space Saving** – weighing only 13 pounds (without film), the small, sturdy machine fits any tabletop. Or use the optional Wall Mount to position it above the packing area, saving even more space.
- **Innovative** – combines the best of NOVUS® and CELL-O® air cushion systems.
- **Fast** – dispenses air cushions at 25 linear feet per minute.
- **Versatile** – one machine makes six different air cushions that fit most shipping needs.
- **Easy to Operate** – Smart machine “reads” film and automatically selects correct air fill and seal temperature settings using RFID technology. Film roll changes take seconds.
- **Reliable** – virtually maintenance free.

## Machine Specifications:

Length	14 inches
Width	13 inches
Height	11 inches
Weight (without film)	13 pounds

## Film Specifications:

(Dimensions may vary slightly.)

### NOVUS Film Roll:

LDPE, un-inflated: 15.5" W x 656' L  
6.5" diameter; 13.5 lbs.

### CELL-O Film Roll:

LDPE, un-inflated: 8" W x 1066' L  
6.5" diameter; 8 lbs.



Supplied By: **The Cary Company**



Ph: 630-629-6600

[www.thecarycompany.com](http://www.thecarycompany.com)

# MINI PAK'R™ Air Cushion Machine

## OPTIONAL WALL MOUNT KIT

When space is an issue, use the optional Wall Mount Kit to install the MINI PAK'R™ machine above the work area. Kit includes wood screws, concrete anchors and toggle bolts so it can be used on any wall surface.



1 Hold the base plate up to the wall at the desired height and adjust position so the top surface is level (a leveling tool or tape measure is required). With a pencil mark four drill hole locations on the wall.



2 Drill pilot holes for the chosen type of wall mounting bolts.



3 Install the base plate with mounting bolts and firmly tighten the mounting bolts into the wall.



4 Mount the Wall Mount Bracket to the MINI PAK'R machine. Use Socket Head Screws to attach the MINI PAK'R machine to the Wall Mount Bracket.



5 Position the Wall Mount Bracket on the Wall Anchor Plate studs.



6 Install and tighten the Hex Nuts.



Supplied By: **The Cary Company**  
 Ph: 630-629-6600  
[www.thecarycompany.com](http://www.thecarycompany.com)